
AMS Ltd, Unit 21 Mead Park Industrial Estate, River Way, Harlow, Essex, CM20 2SE

Tel: 01992 460 111

Email: sales@amsmailingsystems.co.uk Web: www.amsmailingsystems.co.uk





The AMS Data & Barcode Verification System is simply that! A scanner & software package that checks that your codes are scannable and that your barcodes conform to your pre-set requirements such as:

- Sequential checking Alphanumeric, numeric, ascending & descending, upper & lower case
- Grade checking Check your codes conform to a minimum grade quality
- **Database creation** Create a database from the codes scanned and export to a csv file
- **Duplication checking -** Checking to see if a code has been seen before in the same database
- Pattern checking Checking that each code contains the correct fixed character in the right places
- **Image Capture & Quality Reporting** Capture each barcode or document image along with its quality report.

The AMS Data & Barcode Verification System can reduce costly re-runs, postage wastage, and minimise business risks.


It can also help to provide mailers with a high level of assurance that a barcode (such as the Royal Mail MailmarkTM) is scannable by sorting machinery and acceptable with certain grading standards.

This simple system can be fitted to almost any printing and finishing equipment and can be configured to suit your exact requirements. We can provide either a very simple low cost solution, with just the software (suitable PC or laptop required) and a barcode scanner to verify the codes, or a complete solution including a high capacity high performance PC's with image capture scanners.

The software, whilst simple to use and learn is also customisable should you need some specific code written or added for your organisation, this may be done as a free future feature release or quoted for prompt delivery.

Features

Verification of barcode readability
Sequential checking
Grade checking
Database creation
Pattern checking
Image Capture & Quality Reporting
Job Archiving
Session Counters
User Management Levels
Host Stop or Pause Signal, High or Low outputs
Tower light outputs.



Barcode Scanner - no image capture

Code resolution ≥ 0.1mm

Exchangeable illumination options

60Hz, WVGA resolution

30mm-300mm reading distance

Supported Barcode Formats:

GS1-128/EAN128

UPC/GTIN/EN

Interleaved 2 of 5

Pharmacode & GS1 Databar

Code 39, Code 128, Codabar, Code 32, Code 93

Supported 2D codes:

DataMatrix ECC200

MaxiCode

GS1 DataMatrix

QR code

Barcode Scanner - with image capture

1.9 MPx Camera (1600px x 1200px resolution)

Code resolution ≥ 0.1mm

Adjustable focus

Exchangeable illumination options

50 Hz scanning frequency @ 1.9 MPx

50-2200mm reading distance

Supported Barcode Formats:

GS1-128/EAN128

UPC/GTIN/EN

Interleaved 2 of 5

Pharmacode & GS1 Databar

Code 39, Code 128, Codabar, Code 32, Code 93

Supported 2D codes:

DataMatrix ECC200


MaxiCode

GS1 DataMatrix

QR code

PC Options

Dell High-end PC Windows 10 (64bit) I7 Processor 16GB DDR4 RAM 256GB SSD system memory 4 TB HDD Data storage





Email: sales@amsmailingsystems.co.uk
Web: www.amsmailingsystems.co.uk Tel: 01992 460 111